


# Solenoid valve CPE18-M1H-5L-QS-8

Part number: 163150

**FESTO**



## Data sheet

| Feature   | Value                                    |
|---|--|
| Valve function  | 5/2-way, monostable                      |
| Type of actuation                                     | Electric                                 |
| Construction width                                    | 18 mm                                    |
| Standard nominal flow rate (standardised to DIN 1343) | 850 l/min                                |
| pneumatic working port                                | QS-8                                     |
| Operating voltage                                     | 24V DC                                   |
| Operating pressure                                    | 0.25 MPa...1 MPa<br>2.5 bar...10 bar     |
| Design  | Piston gate valve                        |
| Type of reset   | Pneumatic spring                         |
| Approval  | c UL us - Recognized (OL)                |
| Maritime classification                               | See certificate                          |
| Certificate issuing authority                         | DNV-TAA000032X<br>UL MH19482             |
| Degree of protection                                  | IP65<br>With plug socket<br>To IEC 60529 |
| Nominal size  | 8 mm                                     |
| Exhaust-air function                                  | With flow control option                 |
| Sealing principle                                     | Soft                                     |
| Mounting position                                     | optional                                 |
| Manual override                                       | Detenting via accessory<br>Non-detenting |
| Type of piloting                                      | Pilot actuated                           |
| Pilot air supply                                      | Internal                                 |
| Flow direction  | Non-reversible                           |
| Valve position code                                   | Inscription label holder                 |
| lap   | Overlap                                  |
| Switching time off                                    | 20 ms                                    |
| Switching time on                                     | 26 ms                                    |
| Duty cycle  | 100%                                     |
| Max. positive test pulse with 0 signal                | 3300 µs                                  |
| Max. negative test pulse with 1 signal                | 3100 µs                                  |

| Feature                            | Value  |
|------------------------------------|--|
| Characteristic coil data           | 24 V DC: 1.5 W   |
| Permissible voltage fluctuations   | -15%/+10%  |
| Operating medium                   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Vibration resistance               | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6           |
| Shock resistance                   | Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27                          |
| Corrosion resistance class CRC     | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity             | VDMA24364-B1/B2-L  |
| Media temperature                  | -5 °C...50 °C  |
| Ambient temperature                | -5 °C...50 °C  |
| Electrical connection              | Type C   |
| Type of mounting                   | With through-hole  |
| Pilot exhaust port 82              | M5   |
| Pilot exhaust port 84              | M5   |
| Pilot air port 12                  | M5   |
| Pilot air port 14                  | M5   |
| Pneumatic connection, port 1       | QS-8   |
| Pneumatic connection, port 2       | QS-8   |
| Pneumatic connection, port 3       | G1/4   |
| Pneumatic connection, port 4       | QS-8   |
| Pneumatic connection, port 5       | G1/4   |
| Note on materials                  | RoHS-compliant   |
| Material seals                     | NBR  |
| Material housing                   | Die-cast aluminium   |