


# Flat cylinder DZH-63- -PPV-A-S6

Part number: 16534

**FESTO**



## Data sheet

Feature	Value
Stroke	1 mm...1000 mm
Piston diameter	63 mm Equivalent diameter
Torsional backlash at piston rod +/-	0.67 deg
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Mode of operation	Double-acting
Design	Piston Piston rod
Position detection	Via proximity switch
Variants	Heat-resistant seals max. 120°C
Protection against torque/guide	Oval piston
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...120 °C
Cushioning length	23 mm
Max. torque for protection against torsion	2 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	1682 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	1870 N
Additional weight per 10 mm stroke	80 g
Basic weight for 0 mm stroke	1690 g
Type of mounting	Via female thread With accessories Either:
Pneumatic connection	G3/8
Note on materials	RoHS-compliant
Material cover	Aluminium
Material seals	TPE-U(PU)

Feature	Value
Material housing	Aluminium
Material piston rod	High-alloy steel