

Guided drive DFM-32-100-P-A-GF

Part number: 170860

FESTO



Data sheet

| Feature | Value |
|--|--|
| Distance from centre of gravity of load to yoke plate xs | 50 mm |
| Stroke | 100 mm |
| Piston diameter | 32 mm |
| Operating mode, drive unit | Yoke |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | optional |
| Guide | Plain-bearing guide |
| Design | Guidance |
| Position detection | Via proximity switch |
| Operating pressure | 0.15 MPa...1 MPa 1.5 bar...10 bar |
| Max. speed | 0.8 m/s |
| Mode of operation | Double-acting |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom class | Class 7 according to ISO 14644-1 |
| Ambient temperature | -20 °C...80 °C |
| Impact energy in end positions | 0.4 Nm |
| Max. force Fy | 1227 N |
| Max. force Fy static | 1227 N |
| Max. force Fz | 1227 N |
| Max. force Fz static | 1227 N |
| Max. moment Mx | 47.84 Nm |
| Max. torque Mx static | 47.84 Nm |
| Max. moment My | 35.57 Nm |
| Max. torque My static | 35.57 Nm |
| Max. moment Mz | 35.57 Nm |
| Max. torque Mz static | 35.57 Nm |
| Max. permissible torque load Mx as a function of stroke | 7.08 Nm |

| Feature | Value |
|--|----------------------------|
| Max. effective load dependent upon stroke at defined distance xs | 150 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 415 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 482 N |
| Moving mass | 1564 g |
| Product weight | 3111 g |
| alternative connections | See product drawing |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Material cover | Wrought aluminium alloy |
| Material seals | NBR |
| Material housing | Wrought aluminium alloy |
| Material piston rod | High-alloy stainless steel |