

Manifold block CPE18-PRSG-2

Part number: 164970

FESTO



Data sheet

Feature	Value
Max. number of valve positions	2
Burst pressure	3 MPa 30 bar 435 psi
Operating pressure	-0.09 MPa...1 MPa
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	170 g
Mounting method for sub-base	With through-hole With H-rail
Pneumatic connection, port 1	G1/2
Note on materials	RoHS-compliant
Material housing	PA-reinforced