

Guided drive DFM-25-30-P-A-KF

Part number: 170924

FESTO



Data sheet

Feature	Value
Distance from centre of gravity of load to yoke plate xs	50 mm
Stroke	30 mm
Piston diameter	25 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Guidance
Position detection	Via proximity switch
Operating pressure	0.15 MPa...1 MPa 1.5 bar...10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 7 according to ISO 14644-1
Ambient temperature	-5 °C...60 °C
Impact energy in end positions	0.3 Nm
Max. force Fy	863 N
Max. force Fy static	1060 N
Max. force Fz	863 N
Max. force Fz static	1060 N
Max. moment Mx	29.35 Nm
Max. torque Mx static	36.04 Nm
Max. moment My	12.52 Nm
Max. torque My static	15.37 Nm
Max. moment Mz	12.52 Nm
Max. torque Mz static	15.37 Nm
Max. permissible torque load Mx as a function of stroke	5.43 Nm

Feature	Value
Max. effective load dependent upon stroke at defined distance xs	102 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	247 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	295 N
Moving mass	626 g
Product weight	1278 g
Centre of gravity of moving mass as a function of stroke	28.2 mm
alternative connections	See product drawing
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel