


# ISO cylinder

## DSBF-C-100-125-PPSA-N3-R

Part number: 1782828

FESTO



## Data sheet

| Feature  | Value  |
|--|--|
| Stroke   | 125 mm   |
| Piston diameter  | 100 mm   |
| Piston rod thread  | M20x1.5  |
| Cushioning   | Self-adjusting pneumatic end-position cushioning   |
| Mounting position  | optional   |
| Conforms to standard   | ISO 15552  |
| Piston-rod end   | Male thread  |
| Design   | Piston<br>Piston rod<br>Profile barrel   |
| Position detection   | Via proximity switch   |
| Operating pressure   | 0.04 MPa...1.2 MPa<br>0.4 bar...12 bar   |
| Mode of operation  | Double-acting  |
| Operating medium   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 3 - high corrosion stress  |
| LABS (PWIS) conformity                                       | VDMA24364-B2-L   |
| Ambient temperature  | -20 °C...80 °C   |
| Impact energy in end positions                               | 2.5 J  |
| Cushioning length  | 31 mm  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke  | 4418 N   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 4712 N   |
| Moving mass  | 1533 g   |
| Moving mass for 0 mm stroke                                  | 1045 g   |
| Additional moving mass per 10 mm stroke                      | 39 g   |
| Product weight   | 5876 g   |
| Basic weight for 0 mm stroke                                 | 4551 g   |
| Additional weight per 10 mm stroke                           | 106 g  |
| Type of mounting   | Via female thread<br>With accessories<br>Either:   |

| Feature                   | Value                            |
|---------------------------|----------------------------------|
| Pneumatic connection      | G1/2                             |
| Note on materials         | RoHS-compliant                   |
| Material cover            | Die-cast aluminium, coated       |
| Material piston seal      | TPE-U(PU)                        |
| Material piston           | Wrought aluminium alloy          |
| Material piston rod       | High-alloy stainless steel       |
| Material piston rod wiper | TPE-U(PU)                        |
| Buffer seal material      | TPE-U(PU)                        |
| Cushioning boss material  | POM                              |
| Material cylinder barrel  | Anodised wrought aluminium alloy |
| Material nut              | High-alloy stainless steel       |
| Material bearing          | POM                              |
| Material collar screws    | Galvanised steel                 |