


ISO cylinder CRDNG-125- -PPV-A-S2

Part number: 185288

FESTO



Data sheet

Feature	Value
Stroke	10 mm...2000 mm
Piston diameter	125 mm
Piston rod thread	M27x2
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Conforms to standard	ISO 15552
Piston-rod end	Male thread
Design	Piston Piston rod Tie rod Cylinder barrel
Position detection	Via proximity switch
Variants	Through piston rod
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitable for use with food	See supplementary material information
Ambient temperature	-20 °C...80 °C
Cushioning length	40 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	6881 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	6881 N
Moving mass for 0 mm stroke	3239 g
Additional moving mass per 10 mm stroke	128 g
Basic weight for 0 mm stroke	16402 g
Additional weight per 10 mm stroke	220 g
Type of mounting	Via female thread With accessories Either:

Feature	Value
Pneumatic connection	G1/2
Material cover	Stainless steel casting
Material seals	TPE-U(PU)
Material housing	High-alloy stainless steel
Material piston	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel
Material cylinder barrel	High-alloy stainless steel
Material nut	High-alloy stainless steel
Material bearing	POM
Material collar nut	High-alloy stainless steel
Material tie rod	High-alloy stainless steel