


ISO cylinder

DSBF-C-125-100-PPVA-N3-R

Part number: 1785016

FESTO



Data sheet

Feature	Value
Stroke	100 mm
Piston diameter	125 mm
Piston rod thread	M27x2
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Conforms to standard	ISO 15552
Piston-rod end	Male thread
Design	Piston Piston rod Profile barrel
Position detection	Via proximity switch
Operating pressure	0.02 MPa...1 MPa 0.2 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...80 °C
Impact energy in end positions	3.3 J
Cushioning length	45 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	6881 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	7363 N
Moving mass	2875 g
Moving mass for 0 mm stroke	2245 g
Additional moving mass per 10 mm stroke	63 g
Product weight	8558 g
Basic weight for 0 mm stroke	6928 g
Additional weight per 10 mm stroke	163 g
Type of mounting	Via female thread With accessories Either:

Feature	Value
Pneumatic connection	G1/2
Note on materials	RoHS-compliant
Material cover	Die-cast aluminium, coated
Material piston seal	TPE-U(PU)
Material piston	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel
Material piston rod wiper	TPE-U(PU)
Buffer seal material	TPE-U(PU)
Cushioning boss material	POM
Material cylinder barrel	Anodised wrought aluminium alloy
Material nut	High-alloy stainless steel
Material bearing	POM
Material collar screws	Galvanised steel