

# Short-stroke cylinder ADVC-6-10-A-P-A

Part number: 188065

**FESTO**



## Data sheet

| Feature  | Value  |
|--|--|
| Stroke   | 10 mm  |
| Piston diameter  | 6 mm   |
| Cushioning   | Elastic cushioning rings/plates at both ends   |
| Mounting position  | optional   |
| Mode of operation  | Double-acting  |
| Design   | Piston<br>Piston rod   |
| Position detection   | Via proximity switch   |
| Operating pressure   | 0.15 MPa...0.8 MPa<br>1.5 bar...8 bar<br>21.75 psi...116 psi                               |
| Operating medium   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                                       | VDMA24364-B1/B2-L  |
| Ambient temperature  | -20 °C...80 °C   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke  | 13 N   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 17 N   |
| Moving mass  | 2 g  |
| Product weight   | 16 g   |
| Type of mounting   | With through-hole<br>With accessories<br>Either:   |
| Pneumatic connection   | M3   |
| Note on materials  | RoHS-compliant   |
| Material cover   | Wrought aluminium alloy<br>Anodised  |
| Material seals   | NBR<br>TPE-U(PU)   |
| Material housing   | Wrought aluminium alloy<br>Anodised  |
| Material piston rod  | High-alloy steel   |