


Short-stroke cylinder AEVC-4-5-P

Part number: 188051

FESTO



Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	4 mm
Spring return force with retracted piston rod	1 N
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Pushing Single-acting
Design	Piston Piston rod
Position detection	Without
Operating pressure	0.25 MPa...0.8 MPa 2.5 bar...8 bar 36.25 psi...116 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	4.9 N
Moving mass	0.2 g
Product weight	4 g
Type of mounting	With through-hole With accessories Either:
Pneumatic connection	M3
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy Anodised
Material seals	HNBR NBR
Material housing	Wrought aluminium alloy Anodised

Feature	Value
Material piston rod	Wrought aluminium alloy Anodised