


Short-stroke cylinder AEVC-100-25-I-P-A

Part number: 188325

FESTO



Data sheet

Feature	Value
Stroke	25 mm
Piston diameter	100 mm
Spring return force with retracted piston rod	140 N
Based on standard	ISO 6431 Hole pattern VDMA 24562
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Pushing Single-acting
Design	Piston Piston rod
Position detection	Via proximity switch
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar 14.5 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	4503 N
Moving mass	604 g
Product weight	2250 g
Type of mounting	With through-hole With accessories Either:
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy Anodised
Material seals	TPE-U(PU)

Feature	Value
Material housing	Wrought aluminium alloy Anodised
Material piston rod	High-alloy steel