

Suction cup complete holder

ESH-HB-5-G

Part number: 189211

FESTO



Data sheet

Feature	Value
Nominal size	8.5 mm
Volume	1.921 cm ³
Mounting position	optional
Design	Vacuum port on side
Correlation to suction-cup holder	Size 5
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C...60 °C
Product weight	91 g
Type of mounting	Via female thread
Suction cup mounting	M10
Vacuum connection	G1/8
Note on materials	RoHS-compliant
Material retaining bracket	Aluminium Nickel-plated brass POM Tempered steel High-alloy steel