

Suction cup complete ESS-80-SF

Part number: 189321

FESTO



Data sheet

| Feature | Value |
|---|---|
| Min. workpiece radius | 400 mm |
| Nominal size | 6 mm |
| Suction cup diameter | 80 mm |
| Suction cup volume | 19.312 cm ³ |
| Position of connection | Top |
| Mounting position | optional |
| Correlation to suction-cup holder | Size 5 |
| Suction cup shape | Round, flat |
| Operating pressure | -95 kPa...0 kPa -0.95 bar...0 bar -13.775 psi...0 psi |
| Nominal operating pressure | -70 kPa -0.7 bar -10.15 psi |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:::-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| Suitable for use with food | See supplementary material information |
| Ambient temperature | -10 °C...200 °C |
| Holding force at nominal operating pressure | 309.7 N |
| Lateral force at nominal operating pressure | 139.5 N |
| Product weight | 133 g |
| Type of mounting | Via vacuum port |
| Vacuum connection | M10 |
| Colour | grey |
| Shore hardness | 60 +/- 5 |
| Material screwed plug | POM Nickel-plated steel Steel, galvanised and chrome-plated |
| Note on materials | RoHS-compliant |
| Material suction cup | FPM |