


# Tandem cylinder DNCT-4'''- -PPV-A-S6

Part number: 191222

FESTO



## Data sheet

| Feature                            | Value  |
|------------------------------------|--|
| Stroke                             | 3 mm...500 mm  |
| Based on standard                  | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)                  |
| Cushioning                         | Pneumatic cushioning, adjustable at both ends  |
| Mode of operation                  | Double-acting  |
| Operating pressure                 | 0.06 MPa...1 MPa<br>0.6 bar...10 bar   |
| Operating medium                   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC     | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity             | VDMA24364-B2-L   |
| Cushioning length                  | 32 mm  |
| Pneumatic connection               | 1/2 NPT  |
| Note on materials                  | RoHS-compliant   |
| Material cover                     | Die-cast aluminium   |
| Material seals                     | FPM  |
| Material housing                   | Wrought aluminium alloy  |
| Material piston rod                | High-alloy steel   |