


Air reservoir VZS-20-B

Part number: 192161

FESTO



Data sheet

Feature	Value
Volume	20 l
Mounting position	Condensate drain underneath
Conforms to standard	EN 286-1
Operating pressure	-0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.775 psi...232 psi
CE mark (see declaration of conformity)	In accordance with EU Directive on Simple Pressure Vessels
Operating medium	Compressed air to ISO 8573-1:2010 [-::-] Nitrogen
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...100 °C
Ambient temperature	-10 °C...100 °C
Max. tightening torque for connecting thread	130 Nm
Max. tightening torque for condensate drain	27 Nm
Product weight	9000 g
Type of mounting	With through-hole
Condensate drain connection	G3/8
Pneumatic connection	G1
Material air reservoir	Powder-coated steel