


Vacuum generator VN-14-H-T4-PI4-VI5-RI5

Part number: 193502

FESTO



Data sheet

Feature	Value
Nominal size, Laval nozzle	1.4 mm
Grid dimension	18 mm
Mounting position	optional
Ejector characteristic	High vacuum Standard
Design	T-shape
Operating pressure for max. suction flow rate	5.1 bar
Operating pressure	1 bar...8 bar
Operating pressure for max. vacuum	5 bar
Max. vacuum	88 %
Nominal operating pressure	6 bar
Max. suction flow rate against atmosphere	51.6 l/min
Air supply time at nominal operating pressure	0.5 s
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	0 °C...60 °C
Ambient temperature	0 °C...60 °C
Max. tightening torque	0.5 Nm
Product weight	36 g
Type of mounting	With through-hole With accessories
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 3	G1/4
Vacuum connection	G1/4
Material connecting thread	Anodised wrought aluminium alloy
Note on materials	RoHS-compliant
Material seals	NBR
Material receiver nozzle	POM
Material housing	POM-reinforced
Material transmitter nozzle	Wrought aluminium alloy