


Vacuum generator VN-05-N-I3-PQ2-VQ2

Part number: 193635

FESTO



Data sheet

Feature	Value
Nominal size, Laval nozzle	0.45 mm
Grid dimension	13 mm
Mounting position	optional
Ejector characteristic	High suction rate Inline
Design	Straight shape
Operating pressure for max. suction flow rate	6 bar
Operating pressure	1 bar...8 bar
Nominal operating pressure	6 bar
Max. suction flow rate against atmosphere	12 l/min
Air supply time at nominal operating pressure	1.57 s
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	0 °C...60 °C
Ambient temperature	0 °C...60 °C
Product weight	16 g
Type of mounting	In-line installation
Pneumatic connection, port 1	QS-6
Pneumatic connection, port 3	Not ducted
Vacuum connection	QS-6
Note on materials	RoHS-compliant
Material seals	NBR
Material receiver nozzle	POM
Material housing	POM-reinforced
Material transmitter nozzle	Wrought aluminium alloy
Material fitting	Brass Nickel-plated