

Round cylinder DSNU-63- -

Part number: 193995

FESTO



Data sheet

Feature	Value
Stroke	1 mm...500 mm
Piston diameter	63 mm
Cushioning	Elastic cushioning rings/plates at both ends Self-adjusting pneumatic end-position cushioning Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Design	Piston Piston rod Cylinder barrel
Position detection	Via proximity switch
Variants	Extended male piston rod thread Piston rod with female thread Custom thread on the piston rod Piston rod with male thread shortened at one end Extended piston rod Clamping unit on the piston rod Axial supply port With direct mounting Lateral supply port Metal scraper With protection against rotation High corrosion protection Dust protection Uniform, slow movement Low friction Through piston rod Heat-resistant seals max. 120°C Piston rod at one end
Protection against torque/guide	Square piston rod
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Double-acting
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity)	To UK EX instructions
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)

Feature	Value
Explosion protection	Zone 1 (ATEX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 21 (UKEX) Zone 22 (ATEX)
ATEX category gas	II 2G
ATEX category dust	II 2D
Explosion ignition protection type for gas	Ex h IIC T4 Gb
Explosion ignition protection type for dust	Ex h IIIC T120°C Db
Explosion ambient temperature	-20°C ≤ Ta ≤ +60°C
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress 3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L VDMA24364 zone III
Ambient temperature	-20 °C...120 °C
Cushioning length	21 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	1682 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	1870 N
Moving mass for 0 mm stroke	459 g
Additional moving mass per 10 mm stroke	25 g
Basic weight for 0 mm stroke	1445 g
Additional weight per 10 mm stroke	44 g
Type of mounting	With accessories
Pneumatic connection	G3/8
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR TPE-U(PU)
Material piston rod	High-alloy stainless steel
Material cylinder barrel	High-alloy stainless steel