

Flat cylinder

DZF-2 1 1/2"-1"-A-P-A

Part number: 194264

FESTO



Data sheet

Feature	Value
Stroke	1 in
Piston diameter	2 1/2"
Torsional backlash at piston rod +/-	0.4 deg
Cushioning	Elastic cushioning rings/plates at both ends
Mode of operation	Double-acting
Protection against torque/guide	Oval piston
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	1682 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	1870 N
Moving mass for 0 mm stroke	337 g
Additional moving mass per 10 mm stroke	13 g
Additional weight per 10 mm stroke	25 g
Basic weight for 0 mm stroke	1379 g
Pneumatic connection	1/4 NPT
Material cover	Aluminium
Material seals	FPM TPE-U(PU)
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy steel