


Solenoid valve MFH-5-1/8-S-B

Part number: 19759

FESTO



Data sheet

| Feature | Value |
|---|--|
| Valve function | 5/2-way, monostable |
| Type of actuation | Electric |
| Construction width | 26 mm |
| Standard nominal flow rate (standardised to DIN 1343) | 750 l/min |
| pneumatic working port | G1/8 |
| Operating pressure | 0 MPa...1 MPa 0 bar...10 bar |
| Design | Poppet seat |
| Type of reset | Mechanical spring |
| Nominal size | 5 mm |
| Sealing principle | Soft |
| Mounting position | optional |
| Manual override | Non-detenting |
| Type of piloting | Pilot actuated |
| Pilot air supply | External |
| Flow direction | Non-reversible |
| lap | Underlap |
| Pilot pressure | 0.2 MPa...1 MPa 2 bar...10 bar |
| b value | 0.34 |
| C value | 3 l/sbar |
| Max. switching frequency | 3 Hz |
| Switching time off | 30 ms |
| Switching time on | 10 ms |
| Max. positive test pulse with 0 signal | 2200 µs |
| Max. negative test pulse with 1 signal | 3700 µs |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -40 °C...60 °C |

| Feature | Value |
|------------------------------|--|
| Media temperature | -10 °C...60 °C |
| Pilot medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -5 °C...40 °C |
| Product weight | 220 g |
| Electrical connection | Via F coil, to be ordered separately |
| Type of mounting | On PR rail With through-hole Either: |
| Pilot exhaust port 84 | M5 |
| Pilot air port 14 | G1/8 |
| Pneumatic connection, port 1 | G1/8 |
| Pneumatic connection, port 2 | G1/8 |
| Pneumatic connection, port 3 | G1/8 |
| Pneumatic connection, port 4 | G1/8 |
| Pneumatic connection, port 5 | G1/8 |
| Note on materials | RoHS-compliant |
| Material seals | NBR TPE-U(PU) |
| Material housing | Die-cast aluminium |