

# ISO cylinder DSBG-160-200-PPVA-N3

Part number: 2029469

FESTO



## Data sheet

| Feature  | Value  |
|--|--|
| Stroke   | 200 mm   |
| Piston diameter  | 160 mm   |
| Piston rod thread  | M36x2  |
| Cushioning   | Pneumatic cushioning, adjustable at both ends  |
| Mounting position  | optional   |
| Conforms to standard   | ISO 15552  |
| Piston-rod end   | Male thread  |
| Design   | Piston<br>Piston rod<br>Tie rod<br>Cylinder barrel   |
| Position detection   | Via proximity switch   |
| Variants   | Piston rod at one end  |
| Operating pressure   | 0.06 MPa...1 MPa<br>0.6 bar...10 bar   |
| Mode of operation  | Double-acting  |
| Operating medium   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity                                       | VDMA24364-B1/B2-L  |
| Ambient temperature  | -20 °C...80 °C   |
| Impact energy in end positions                               | 3.3 J  |
| Cushioning length  | 48 mm  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke  | 11310 N  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 12064 N  |
| Moving mass  | 6232 g   |
| Moving mass for 0 mm stroke                                  | 4292 g   |
| Additional moving mass per 10 mm stroke                      | 97 g   |
| Product weight   | 15911 g  |
| Basic weight for 0 mm stroke                                 | 11751 g  |
| Additional weight per 10 mm stroke                           | 208 g  |

| Feature                   | Value  |
|---------------------------|--|
| Type of mounting          | Via female thread<br>With accessories<br>Either: |
| Pneumatic connection      | G3/4   |
| Note on materials         | RoHS-compliant                                   |
| Material cover            | Cast aluminium, coated                           |
| Material piston seal      | NBR  |
| Material piston           | Cast aluminium                                   |
| Material piston rod       | High-alloy steel                                 |
| Material piston rod wiper | NBR  |
| Buffer seal material      | TPE-U(PU)  |
| Cushioning boss material  | POM  |
| Material cylinder barrel  | Smooth-anodised wrought aluminium alloy          |
| Material nut              | Galvanised steel                                 |
| Material bearing          | Metal polymer compound                           |
| Material collar nut       | Galvanised steel                                 |
| Material tie rod          | High-alloy steel                                 |