


Guide unit EAGF-V2-KF-80-

Part number: 2608528

FESTO



Data sheet

Feature	Value
Size	80
Stroke	1 mm...550 mm
Reversing backlash theoretical	0 µm
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Guidance
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...80 °C
Max. force Fy	2300 N
Max. force Fy static	3120 N
Max. force Fz	2300 N
Max. force Fz static	3120 N
Max. moment Mx	170 Nm
Max. torque Mx static	231 Nm
Max. moment My	191 Nm
Max. torque My static	259 Nm
Max. moment Mz	191 Nm
Max. torque Mz static	259 Nm
Displacement force	40 N
Moving mass for 0 mm stroke	5166 g
Basic weight for 0 mm stroke	10517 g
Additional weight per 10 mm stroke	76 g
Additional moving mass per 10 mm stroke	76 g
Centre of gravity at 0 mm stroke	54 mm
Centre of gravity additional of moving mass per 10 mm	3.8 mm
Type of mounting	Via female thread
Note on materials	RoHS-compliant
Material guide component	Tempered steel
Material housing	Wrought aluminium alloy Anodised

Feature	Value
Material yoke plate	Steel