

Bus module CPX-E-PN

Part number: 4080497

FESTO



RD	0	1	RD
BU	2	3	BU

Data sheet

Feature	Value
Dimensions (W x L x H)	42.2 mm x 76.5 mm x 125.8 mm
Grid dimension	18.9 mm
Type of mounting	With H-rail
Max. number of modules	10
Product weight	145 g
Mounting position	Vertical Horizontal
Ambient temperature	-5 °C...50 °C
Note on ambient temperature	-5 - 60°C for vertical installation
Storage temperature	-20 °C...70 °C
Relative air humidity	95 % Non-condensing
Degree of protection	IP20
Corrosion resistance class CRC	0 - No corrosion stress
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Protection against direct and indirect contact	PELV
LABS (PWIS) conformity	VDMA24364 zone III
CE mark (see declaration of conformity)	To EU EMC Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC mark	KC-EMV
Approval	RCM trademark c UL us listed (OL)
Certificate issuing authority	UL E239998
Note on materials	RoHS-compliant
Material housing	PA

Feature	Value
Diagnostics via LED	Force mode Network fault Network status, port 1 Network status, port 2 Power supply, electronics/sensors Load power supply System fault Service required
Diagnostics via bus	Wire break Short circuit PROFIsafe addresses different Parameterisation error Upper limit value violated Overtemperature Lower limit value not observed Undervoltage
Fieldbus interface	Ethernet
Field bus, protocol	PROFINET IRT PROFINET RT
Field bus, connection type	2x socket
Field bus, connection system	RJ45
Field bus, connection pattern	8
Field bus interface, electrical isolation	yes
Field bus interface, transmission rate	100 Mbit/s
Max. address volume, inputs	64 Byte
Fieldbus interface, max. address volume for inputs	64 Byte
Note on inputs	62 bytes with I/O diagnostic interface 62 bytes with status bits 64 bytes without diagnostics
Max. address volume, outputs	64 Byte
Fieldbus interface, max. address volume for outputs	64 Byte
Note on outputs	62 bytes with I/O diagnostic interface 64 bytes with status bits 64 bytes without diagnostics
System parameters	Diagnostic memory Fail-safe response Force mode System start
Module parameters	Channel alarms bundling Undervoltage diagnostics Channel alarms for undervoltage Process value representation of analogue modules
Configuration support	GSDML file
Additional functions	LLDP MRP MRPD PROFINET FSU PROFINET I&MO..3, 1..3 retentive memory possible PROFINET shared device S2 system redundancy SNMP
Power supply, function	Electronics and sensors
Power supply, connection type	Terminal strip
Power supply, note on connection type	> 4 A and UL 2x terminal strip for power supply
power supply, connection system	Spring-loaded terminal
Power supply, number of pins/wires	4
Nominal DC operating voltage, electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	± 25%
Power supply, conductor diameter	0.2 mm²...1.5 mm²
Power supply, note on conductor diameter	0.2 - 2.5 mm² for flexible conductors without wire ferrule
Max. power supply	8 A

Feature	Value
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 75 mA
Power failure bridging	20 ms
Reverse polarity protection	24 V sensor supply against 0 V sensor supply