


# Stopper cylinder EFSD-20-PV-M12

Part number: 2942445

**FESTO**



## Data sheet

Feature	Value
Design	Electric stopper cylinder
Size	20
Mounting position	optional
Position detection	With Hall sensor
Corrosion resistance class CRC	1 - Low corrosion stress
Ambient temperature	-10 °C...60 °C
Storage temperature	-20 °C...60 °C
Relative air humidity	0 - 95% Non-condensing
Cushioning length	11.5 mm
Product weight	420 g
Max. cycle frequency	0.33 Hz
Type of mounting	Via mounting kit
Return-stroke time	0.1 s
Advance time	0.1 s
Permissible lateral force during switching operation	20 N
Approval	RCM trademark
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material cover	PA PA-reinforced
Material seals	NBR
Material housing	Hard anodised wrought aluminium alloy
Material piston rod	High-alloy stainless steel
Material screws	Coated steel
Max. current consumption	2 A
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 15%
Type of motor	Stepper motor
KC mark	KC-EMV
CE mark (see declaration of conformity)	To EU EMC Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC

Feature	Value
Degree of protection	IP40
Max. cable length	30 m
Ready status indication	LED
Electrical connection for actuator, connection type	Plugs
Electrical connection for actuator, connection technology	M12x1, A-coded to EN 61076-2-101
Electrical connection for actuator, number of pins/wires	5
Electrical connection actuator, max. current consumption	1.9 A
Electrical connection for sensor, connection type	Plugs
Electrical connection for sensor, connection technology	M12x1, A-coded to EN 61076-2-101
Electrical connection for sensor, number of pins/wires	5
Electrical connection sensor, max. current consumption	0.3 A