

Servo motor EMMT-AS-80-

Part number: 4595815

FESTO



Data sheet

Feature	Value
Ambient temperature	-15 °C...40 °C
Note on ambient temperature	Up to 80°C with derating of -1.5% per degree Celsius
Max. installation height	4000 m
Note on max. installation height	As of 1,000 m: only with derating of -1.0% per 100 m
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 90%
Conforms to standard	IEC 60034
Temperature class as per EN 60034-1	F
Max. winding temperature	155 °C
Rating class as per EN 60034-1	S1
Temperature monitoring	Digital motor temperature transmission via EnDat® 2.2
Motor type to EN 60034-7	IM B5 IM V1 IM V3
Mounting position	optional
Degree of protection	IP40 IP65
Note on degree of protection	IP40 for motor shaft without rotary shaft seal IP65 for motor shaft with rotary shaft seal IP67 for motor housing including connection components
Concentricity, coaxiality, axial runout to DIN SPEC 42955	N
Balance quality	G 2.5
Detent torque	<1.0% of peak torque
Bearing lifetime under nominal conditions	20000 h
Featherkey shaft type	DIN 6885 A 6 x 6 x 22
Interface code, motor out	80P
Electrical connection 1, connection type	Hybrid plug
Electrical connection 1, connector system	M23x1
Electrical connection 1, number of connections/cores	15
Pollution degree	2
Note on materials	RoHS-compliant
Corrosion resistance class CRC	0 - No corrosion stress

Feature	Value
LABS (PWIS) conformity	VDMA24364 zone III
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Approval	RCM trademark German Technical Control Board (TÜV) c UL us - Recognized (OL)
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK regulations for electrical equipment
Certificate issuing authority	TÜV 968/INS 464.00/24 UL E342973
Nominal operating voltage DC	325 V...680 V
Type of winding switch	Star inside
Number of pole pairs	5
Standstill torque	1.43 Nm...4.3 Nm
Nominal torque	1.24 Nm...3.4 Nm
Peak torque	2.8 Nm...13.5 Nm
Nominal rotary speed	3000 rpm
Max. rotational speed	5650 rpm...8950 rpm
Angular acceleration	100000 rad/s ²
Nominal power rating of motor	390 W...1070 W
Continuous stall current	2 A...6.8 A
Nominal motor current	1.7 A...5.5 A
Peak current	5.4 A...27.3 A
Motor constant	0.46 Nm/A...1 Nm/A
Standstill torque constant	0.57 Nm/A...1.17 Nm/A
Voltage constant, phase-to-phase	34.3 mVmin...70.7 mVmin
Phase-phase winding resistance	1.13 Ohm...12.4 Ohm
Phase-phase winding inductance	5.2 mH...39.8 mH
Winding longitudinal inductivity Ld (phase)	3.1 mH...25 mH
Winding cross inductivity Lq (phase)	3.9 mH...29.8 mH
Electric time constant	4.8 ms...7.2 ms
Thermal time constant	42 min...51 min
Thermal resistance	0.65 K/W...0.95 K/W
Total mass moment of inertia of output	0.597 kgcm ² ...2.43 kgcm ²
Product weight	2020 g...4750 g
Permissible axial shaft load	120 N
Permissible radial shaft load	620 N
Rotor position sensor	Absolute single-turn encoder Absolute multi-turn encoder Absolute multi-turn safety encoder
Rotor position encoder interface	EnDat® 22
Rotor position sensor, encoder measuring principle	Inductive
Rotor position transducer resolution	18 bit...19 bit
Brake holding torque	4.5 Nm...7 Nm
Operating voltage DC for brake	24 V
Power consumption, brake	12 W...15 W
Number of emergency stops per hour	1
Mass moment of inertia of brake	0.249 kgcm ² ...0.459 kgcm ²
Switching cycles holding brake	10 million idle actuations (without friction work!)
Safety device	Safety device

Feature	Value
Maximum SIL	Safety integrity level 3 See user documentation
Safety sub-functions up to SIL2	Reliable recording and transmission of single-turn position data
Safety sub-functions up to SIL3	Reliable recording and transmission of single-turn position data, only with additional software function in the servo drive
Maximum PL and category	Performance Level e, Category 3 See user documentation
Safety sub-function up to PL d, Cat. 3	Reliable recording and transmission of single-turn position data
Safety sub-function up to PL e, Cat. 3	Reliable recording and transmission of single-turn position data, only with additional software function in the servo drive
PFHd, subcomponent	15 x 10E-9, encoder
Duration of use Tm, subcomponent	20 years, rotor position sensor
Mean time to failure (MTTF), subcomponent	190 years, rotor position sensor
Energy efficiency	ENEFF (CN) / Class 2