


Trunnion support LNZG-63/80

Part number: 32961

FESTO



Data sheet

Feature	Value
Size	63/80
Based on standard	ISO 15552
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...80 °C
Max. load capacity	6 kN
Product weight	178 g
Note on materials	RoHS-compliant
Material mounting	Wrought aluminium alloy
Material bearing	Polymer