


Compact cylinder DPDM-6-15-PA

Part number: 4830902

FESTO



Data sheet

Feature	Value
Stroke	15 mm
Piston diameter	6 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Double-acting
Design	Piston Piston rod Profile barrel
Position detection	Via proximity switch
Variants	Piston rod at one end
Operating pressure	0.18 MPa...0.8 MPa 1.8 bar...8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi)	17 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	13 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	17 N
Moving mass for 0 mm stroke	2.8 g
Additional moving mass per 10 mm stroke	0.6 g
Basic weight for 0 mm stroke	20.7 g
Additional weight per 10 mm stroke	6.3 g
Type of mounting	With through-hole Via female thread Either:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy

Feature	Value
Material seals	NBR TPE-U(PU)
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy stainless steel