


Linear drive DFPI-200- -

Part number: 5092508

FESTO



Data sheet

Feature	Value
Size of valve actuator	200
Stroke	40 mm...990 mm
Piston diameter	200 mm
Based on standard	ISO 15552
Cushioning	No cushioning
Mounting position	optional
Mode of operation	Double-acting
Design	Piston Piston rod Tie rod Cylinder barrel
Position detection	With integrated displacement encoder
Functional principle of measuring system	Potentiometer
Reverse polarity protection	yes
Operating pressure	0.3 MPa...0.8 MPa 3 bar...8 bar 43.5 psi...116 psi
Nominal operating pressure	0.6 MPa 6 bar
Analogue output	4 - 20 mA
Operational voltage range DC	9 V...30 V
Recommended wiper current	0.1 µA
Max. wiper current, short-time	10 mA
Power supply	2-wire
Approval	RCM trademark
KC mark	KC-EMV
CE mark (see declaration of conformity)	To EU EMC Directive To EU Explosion Protection Directive (ATEX) In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK EX instructions To UK RoHS instructions

Feature	Value
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
ATEX category gas	II 2G
ATEX category dust	II 2D
Explosion ignition protection type for gas	Ex h IIC T4 Gb
Explosion ignition protection type for dust	Ex h IIIC T120°C Db
Explosion ambient temperature	-20°C ≤ Ta ≤ +60°C
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Continuous shock resistance to DIN/IEC 68 Part 2-82	Tested to severity level 2
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...80 °C
Relative air humidity	5 - 100% Condensing Non-condensing
Degree of protection	IP65 IP67 IP69K NEMA 4
Vibration resistance to DIN/IEC 68 Part 2-6	Tested to severity level 2
Ambient temperature	-20 °C...80 °C
Impact energy in end positions	1 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	18080 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	18850 N
Air consumption on return stroke per 10 mm	2.111 l
Air consumption on advance stroke per 10 mm	2.199 l
Moving mass for 0 mm stroke	4800 g
Additional moving mass per 10 mm stroke	89 g
Basic weight for 0 mm stroke	18100 g...19800 g
Additional weight per 10 mm stroke	238 g
Hysteresis	0.4 mm
Non-dependent linearity	±0.05%
Repetition accuracy in ± %FS	1 %FS
Repetition accuracy in ± mm	0.7 mm
Electrical connection	2-pin 3-pin 4-pin 5-pin A-coded Cable connector M16x1.5 M12x1 Straight plug connector/screw terminal Straight plug With specific accessories
Pneumatic connection	G3/8 G1/2 For tubing O.D. 8 mm With specific accessories
Note on materials	RoHS-compliant
Material end cap	Coated wrought aluminium alloy
Material underneath cover	Die-cast aluminium, coated
Material electrical connection	Nickel-plated brass High-alloy stainless steel
Material piston rod	High-alloy stainless steel
Material piston rod wiper	NBR
Pipe material	High-alloy stainless steel

Feature	Value
Material tubing	PE
Material screws	Coated steel High-alloy stainless steel
Material static seals	NBR
Material fitting	Nickel-plated brass High-alloy stainless steel
Material tie rod	High-alloy stainless steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy