

# Compact cylinder DPDM-25-10-S-PA

Part number: 4829800

**FESTO**



## Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	25 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Pushing Single-acting
Design	Piston Piston rod Profile barrel
Position detection	Via proximity switch
Variants	Piston rod at one end
Operating pressure	0.15 MPa...0.8 MPa 1.5 bar...8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi)	269 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	269 N
Moving mass for 0 mm stroke	58 g
Additional moving mass per 10 mm stroke	6.5 g
Basic weight for 0 mm stroke	192 g
Additional weight per 10 mm stroke	33.5 g
Type of mounting	With through-hole Via female thread Either:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	TPE-U(PU)

Feature	Value
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy stainless steel