


Plug NOCC-M-S-SCRJG2PP-C5-PN

Part number: 5195381

FESTO



Data sheet

Feature	Value
Conforms to standard	IEC 61754-24
Protocol	Ethernet PROFINET FOC
Additional functions	Fulfil requirements according to AIDA
Frequency of connection	100
Cable outlet	Straight
Product weight	84 g
Optical connection 1, connection type	Plug
Optical connection 1, design	Rectangular
Optical connection 1, connection technology	SC-RJ to IEC 61754-24
Optical connection 1, number of pins/cores	2
Optical connection 1, occupied pins/wires	2
Optical connection 1, plug pattern	00995772
Optical connection 1, type of mounting	Push-pull with interlock against unintentional pulling
Optical connection 1, ferrule diameter	2.5 mm
Optical connection 2, connection technology	Lock nut
Tightening torque	0.42 Nm
Wire diameter	0.98 mm...1 mm
Type of wire	Polymer fibre
Wavelength	650 nm
Fire test	UL94 V-0
Cable diameter	5.5 mm...10 mm
Degree of protection	IP65 IP67
Note on degree of protection	In assembled state
Ambient temperature	-25 °C...70 °C
Storage temperature	-40 °C...70 °C
LABS (PWIS) conformity	VDMA24364-A1-L
Note on materials	RoHS-compliant
Corrosion resistance class CRC	1 - Low corrosion stress
Material housing	Die-cast zinc, nickel-plated
Housing colour	Silver

Feature	Value
Material seals	NBR TPE
Ferrule material	Copper alloy