


Power supply socket
NECU-M-PPG5PP-C1-PN
Part number: 5195383

FESTO



Dum
my

Data sheet

Feature	Value
Protocol	PROFINET
Approval	c UL us - Recognized (OL)
Certificate issuing authority	UL E328433
Additional functions	Fulfils requirements according to AIDA
Frequency of connection	100
Cable outlet	Straight
Product weight	109 g
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Socket
Electrical connection 1, connector system	Connection pattern PP, coding on pins 2 and 5
Electrical connection 1, number of connections/cores	5
Electrical connection 1, used connections/cores	5
Electrical connection 1, type of mounting	Push-pull with interlock against unintentional pulling
Electrical connection 2, connector system	Spring-loaded terminal
Operational voltage range DC	0 V...24 V
Current rating at 40° C	16 A
Immunity to surge	4 kV
Cable fitting	Pg13.5, hexagon size 22 mm
Cable diameter	9 mm...13 mm
Nominal cross section conductor	0.75 mm²...2.5 mm²
Conductor nominal cross section	AWG18 - 13
Degree of protection	IP65 IP67
Note on degree of protection	In assembled state
Ambient temperature	-40 °C...85 °C

Feature	Value
Storage temperature	-40 °C...85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Fire test	UL94 V-0
Pollution degree	3
Corrosion resistance class CRC	1 - Low corrosion stress
Material housing	Die-cast zinc, nickel-plated
Housing colour	Silver
Material seals	NBR TPE-V
Material electrical contact	Nickel-plated and gold-plated copper alloy