

Branching module MS6N-FRM

Part number: 527677

FESTO



Data sheet

Feature	Value
Mounting position	optional
Design	Branching module
Pressure gauge (ANALOG) or Pressure display (DIGITAL)	Prepared for G1/4 Prepared for G1/8 Via pressure sensor With pressure gauge
Operating pressure	0 bar...20 bar
Standard nominal flow rate in main flow direction 1->2	3200 l/min...14700 l/min
Standard nominal flow rate, outlet upwards	2700 l/min...6000 l/min
Standard nominal flow rate, outlet downwards	2800 l/min...6400 l/min
Operational voltage range AC	0 V...250 V
Operational voltage range DC	0 V...125 V
Approval	c UL us - Recognized (OL)
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Suitable for use with food	See supplementary material information
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	458 g
Note on materials	RoHS-compliant
Material housing	Die-cast aluminium