

# Guided drive DFM-20- -B

Part number: 532316

**FESTO**



## Data sheet

Feature	Value
Stroke	20 mm...400 mm
Piston diameter	20 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends Pneumatic cushioning, adjustable at both ends Shock absorber, soft characteristic curve
Mounting position	optional
Guide	Plain-bearing guide Recirculating ball bearing guide
Design	Guidance
Position detection	Via proximity switch
Variants	Heat-resistant seals max. 120°C
Operating pressure	0.2 MPa...1 MPa 2 bar...10 bar
Mode of operation	Double-acting
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity)	To UK EX instructions
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX)
ATEX category gas	II 2G
Explosion ignition protection type for gas	Ex h IIC T4 Gb
Explosion ambient temperature	-20 °C ≤ Ta ≤ +70 °C
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress 2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...120 °C
Impact energy in end positions	0.1 J...0.2 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	158 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	188 N
alternative connections	See product drawing

Feature	Value
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel