



Vacuum generator VN-07-H-T3-PI4-VI4-RO1-A

Part number: 532632

FESTO



Data sheet

| Feature | Value |
|--|--|
| Nominal size, Laval nozzle | 0.7 mm |
| Grid dimension | 14 mm |
| Silencer design | Open |
| Mounting position | optional |
| Ejector characteristic | Standard High negative pressure |
| Integrated function | Ejector pulse valve, pneumatic Open silencer |
| Design | T-shape |
| Operating pressure for max. suction flow rate | 3 bar |
| Operating pressure | 1 bar...8 bar |
| Operating pressure for max. vacuum | 4.4 bar |
| Max. vacuum | 92 % |
| Nominal operating pressure | 6 bar |
| Max. suction flow rate against atmosphere | 16.2 l/min |
| Air supply time at nominal operating pressure | 1.5 s |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation not possible |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Media temperature | 0 °C...60 °C |
| Recommended cleaning/purification | Soapy water |
| Sound pressure level at nominal operating pressure | 65 dB(A) |
| Ambient temperature | 0 °C...60 °C |
| Max. tightening torque | 0.5 Nm |
| Product weight | 50 g |
| Type of mounting | With through-hole With H-rail With accessories |
| Pneumatic connection, port 1 | G1/8 |
| Pneumatic connection, port 3 | Open silencer |
| Vacuum connection | G1/8 |

| Feature | Value |
|-----------------------------|----------------------------------|
| Material connecting thread | Anodised wrought aluminium alloy |
| Note on materials | RoHS-compliant |
| Material seals | NBR |
| Material receiver nozzle | POM |
| Material housing | PA-reinforced POM-reinforced |
| Material silencer | PE |
| Material screws | Steel |
| Material transmitter nozzle | Wrought aluminium alloy |