

Fine filter
MS12-LFM
 Part number: 535042

FESTO



Data sheet

Feature	Value
Series	MS
Size	12
Design	Fibre filter
Condensate drain	Fully automatic Fully automatic, electrically actuated Manual, non-detenting Manually rotating
Operating pressure	0.08 MPa...2 MPa 0.8 bar...20 bar 11.6 psi...290 psi
Operating medium	Compressed air to ISO 8573-1:2010 [6:-:4] Inert gases
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Storage temperature	-10 °C...60 °C
Type of mounting	In-line installation With accessories Either:
Mounting position	Vertical +/-5°
Material housing	Die-cast aluminium
Material filter	Borosilicate fibre
Material bowl	Wrought aluminium alloy
Note on materials	RoHS-compliant