

Compact cylinder ADN-80-30-I-P-A

Part number: 536367

FESTO



Data sheet

Feature	Value
Stroke	30 mm
Piston diameter	80 mm
Piston rod thread	M12
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Conforms to standard	ISO 21287
Piston-rod end	Female thread
Position detection	Via proximity switch
Variants	Piston rod at one end
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Impact energy in end positions	1.8 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	2827 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	3016 N
Moving mass	356 g
Product weight	1229 g
Type of mounting	With through-hole Via female thread With accessories Either:
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material collar screws	Steel
Material cover	Die-cast aluminium, coated
Material seals	TPE-U(PUR)
Material piston rod	High-alloy steel

Feature	Value
Material cylinder barrel	Smooth-anodised wrought aluminium alloy