



# Proximity sensor SIEH-3B-NS-S-L

Part number: 538265

FESTO



## Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive
Measuring principle	Inductive
Rated operating distance	1 mm
Assured operating distance	0.81 mm
Reduction factors	Aluminium = 0.5 Stainless steel St 18/8 = 0.8 Copper = 0.45 Brass = 0.6 Steel St 37 = 1.0
Ambient temperature	-25 °C...70 °C
Repetition accuracy	0.02 mm
Switching output	NPN
Switching element function	N/O contact
Hysteresis	0.12 mm
Switch-on time	0.02 ms
Max. switching frequency DC	3000 Hz
Max. output current	100 mA
Voltage drop	2 V
Inductive protective circuit	Integrated Output current < 100 mA And switching frequency < 10 Hz
Off-state current	0.1 mA
Short circuit current rating	Pulsed
Operational voltage range DC	10 V...30 V
Residual ripple	20%
No-load supply current	10 mA
Reverse polarity protection	For all electrical connections
Electrical connection	3-pin Cable with plug M8x1

Feature	Value
Cable length	0.15 m
Material cable sheath	TPE-U(PUR)
Material insulating sheath	PVC
Size	3 mm
Type of mounting	Clamped
Mounting type	Flush
Product weight	4 g
Material housing	High-alloy stainless steel
Switching status indication	Yellow LED
Ambient temperature with moving cable	-5 °C...70 °C
Degree of protection	IP67
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Additional information for sensor selection	with increased sensing distance
Electrical output	NPN
Selection of sensor design	Standard