



Proximity sensor SIEF-M8NB-NS-K-L

Part number: 538310

FESTO



Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK regulations for electrical equipment
Measuring principle	Inductive
Rated operating distance	4 mm
Assured operating distance	3.24 mm
Reduction factors	Aluminium = 1.0 Stainless steel St 18/8 = 1.0 Copper = 1.0 Brass = 1.0 Steel St 37 = 1.0
Ambient temperature	-30 °C...85 °C
Repetition accuracy	0.08 mm
Switching output	NPN
Switching element function	N/O contact
Hysteresis	0.12 mm...0.6 mm
Max. switching frequency DC	2000 Hz
Max. output current	150 mA
Voltage drop	1.8 V
Short circuit current rating	Pulsed
Operational voltage range DC	10 V...30 V
Residual ripple	10 %
No-load supply current	15 mA
Reverse polarity protection	For all electrical connections
Electrical connection	3-wire Cable
Cable length	2.5 m

Feature	Value
Material cable sheath	TPE-U(PUR)
Material insulating sheath	PVC
Size	M8
Type of mounting	Via lock nut
Tightening torque	10 Nm
Mounting type	Not flush
Product weight	77 g
Material housing	PA High-alloy stainless steel
Switching status indication	Yellow LED
Ambient temperature with moving cable	0 °C...80 °C
Degree of protection	IP67
Immunity to magnetic fields	Magnetic direct and alternating field
Corrosion resistance class CRC	4 - Very high corrosion stress
Additional information for sensor selection	Reduction factor 1, resistant to magnetic fields
Electrical output	NPN
Selection of sensor design	Standard