


Proximity sensor SIEN-M30NB-PS-K-L-PA

Part number: 538333

FESTO



Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK regulations for electrical equipment
Measuring principle	Inductive
Rated operating distance	15 mm
Assured operating distance	12.15 mm
Reduction factors	Aluminium = 0.35 - 0.5 Stainless steel St 18/8 = 0.6 - 1.0 Copper = 0.25 - 0.45 Brass = 0.35 - 0.5 Steel St 37 = 1.0
Ambient temperature	-25 °C...70 °C
Repetition accuracy	0.3 mm
Switching output	PNP
Switching element function	N/O contact
Hysteresis	0.45 mm...2.25 mm
Max. switching frequency DC	500 Hz
Max. output current	200 mA
Voltage drop	1.8 V
Short circuit current rating	Pulsed
Operational voltage range DC	10 V...30 V
Residual ripple	10 %
No-load supply current	15 mA
Reverse polarity protection	For all electrical connections
Electrical connection	3-wire Cable
Cable length	2.5 m

Feature	Value
Material cable sheath	PVC
Material insulating sheath	PVC
Size	M30
Type of mounting	Via lock nut
Tightening torque	5 Nm
Mounting type	Not flush
Product weight	158 g
Material housing	PA-reinforced
Switching status indication	Yellow LED
Ambient temperature with moving cable	0 °C...70 °C
Degree of protection	IP65 IP67
Corrosion resistance class CRC	4 - Very high corrosion stress
Additional information for sensor selection	with standard sensing distance
Electrical output	PNP
Selection of sensor design	Polyamide housing