

# Valve terminal VTSA-FB-NPT

Part number: 539218

**FESTO**



## Data sheet

Feature	Value
Electrical control	Ethernet Fieldbus Integrated controller
Electrical I/O system	yes
Terminal type	44
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Ambient temperature	-5 °C...50 °C
Storage temperature	-20 °C...60 °C
Relative air humidity	0 - 90%
Degree of protection	IP65 NEMA 4
Corrosion resistance class CRC	0 - No corrosion stress
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Pilot pressure	0.3 MPa...1 MPa 3 bar...10 bar
Operating pressure for valve terminal with internal pilot air supply	0.3 MPa...1 MPa 3 bar...10 bar
LABS (PWIS) conformity	VDMA24364-B1/B2-L
CE mark (see declaration of conformity)	To EU EMC Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC mark	KC-EMV
Approval	BIA C-Tick c UL us - Recognized (OL)
Note on materials	RoHS-compliant
Valve terminal structure	Modular, valve sizes can be mixed
Max. number of valve positions	32
Max. number of pressure zones	32
Type of actuation	Electric

Feature	Value
Valve function	2x2/2-way, monostable, closed 2x3/2-way, monostable, closed 2x3/2-way, open, monostable 2x3/2-way, open/closed, monostable 5/2 double solenoid 5/2-way, bistable, dominant 5/2-way, monostable 5/2-way, monostable, safety function 5/3-way, pressurised 5/3 exhausted 5/3 closed 5/3-way, port 2 pressurised, 4 exhausted
Design	Piston gate valve
Valve size	18 mm 26 mm 42 mm 52 mm 65 mm
Pilot air supply	External Internal
Max. standard nominal flow rate	550 l/min at 18 mm 1100 l/min at 26 mm 1300 l/min at 42 mm 2900 l/min at 52 mm 4000 l/min at 65 mm
Suitability for vacuum	yes
Exhaust-air function	Via throttle plate
pneumatic working port	1/8 NPT 1/4 NPT 3/8 NPT 1/2 NPT QS-6 QS-8 QS-10 QS-12 QS-16
Signal status display	LED
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 10 %