


On/off valve MS4N-EE-1/8-10V24-Z

Part number: 542591

FESTO



Data sheet

| Feature | Value |
|---|--|
| Design | Piston gate valve |
| Type of actuation | Electric |
| Exhaust-air function | Without flow control option |
| Manual override | Non-detenting |
| Type of reset | Mechanical spring |
| Type of piloting | Pilot actuated |
| Valve function | 3/2-way, closed, monostable |
| Operating pressure | 4 bar...10 bar |
| lap | Overlap |
| C value | 4.5 l/sbar |
| b value | 0.5 |
| Standard nominal flow rate (standardised to DIN 1343) | 1000 l/min |
| Duty cycle | 100% |
| Characteristic coil data | 24 V DC: 1.8 W |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| Note on materials | RoHS-compliant |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Media temperature | -10 °C...50 °C |
| Degree of protection | IP65 |
| Ambient temperature | -10 °C...50 °C |
| Suitable for use with food | See supplementary material information |
| Type of mounting | In-line installation With accessories Either: |
| Mounting position | optional |
| Flow direction | Non-reversible |
| Product weight | 273 g |
| Pneumatic connection, port 1 | 1/8 NPT |

| Feature | Value |
|------------------------------|--|
| Pneumatic connection, port 2 | 1/8 NPT |
| Pneumatic connection, port 3 | G1/4 |
| Pilot air supply | Internal |
| Electrical connection | Type C Plugs To DIN EN 175301-803 Square design |
| Material seals | NBR |
| Material housing | Die-cast aluminium |