


Linear gantry DHSL-2DGC25-DGEA25

Part number: 543004

FESTO

comprising rodless drive with passive guide axis and electric cantilever axis, dynamic, precise, electrically positioned. Defined interfaces to Festo's rotary and gripper range. Order as a mounting kit or completely assembled and installed.

Please click above on symbol FAX request, to obtain a non-binding offer to fulfil your requirements.



Data sheet

Feature	Value
Assembly	Linear gantry 3.0
Effective load	0 ... 6 kg
Drive unit, Z axis	DGEA-25
Drive system, Z axis	Electrical DGEA toothed belt drive
Intermediate position, Z axis	Any
Stroke, Z axis	0 ... 800 mm
Repetition accuracy in the end position, Z axis	± 0,05 mm
Repetition accuracy in the intermediate position, Z axis	± 0,05 mm
Drive unit, Y axis	2x DGC-25
Drive system, Y axis	Pneumatic
Stroke, Y axis	0 ... 3,000 mm
Repetition accuracy in the end position, Y axis	± 0,02 mm