

Mini slide DGSL-25-150-PA

Part number: 544037

FESTO



Data sheet

Feature	Value
Stroke	150 mm
Adjustable end position range/length front	110 mm
Adjustable end position range/length rear	49 mm
Piston diameter	32 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Guide	Ball bearing cage guide
Design	Yoke Piston Piston rod Slide
Position detection	Via proximity switch
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar
Max. speed	0.8 m/s
Repetition accuracy	0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 7 according to ISO 14644-1
Ambient temperature	0 °C...60 °C
Impact energy in end positions	0.55 Nm
Cushioning length	1.3 mm
Max. force F _y	4800 N
Max. force F _z	4800 N
Max. moment M _x	130 Nm
Max. moment M _y	80 Nm
Max. moment M _z	80 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	415 N

Feature	Value
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	483 N
Moving mass	2102 g
Product weight	5556 g
alternative connections	See product drawing
Type of mounting	With through-hole
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	HNBR
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel