


# Solenoid valve VZWM-L-M22C-N14-F4

Part number: 546154

FESTO



## Data sheet

Feature	Value
Design	Diaphragm valve servo-controlled
Type of actuation	Electric
Sealing principle	Soft
Mounting position	Preferably vertical
Type of mounting	In-line installation
Connection Process valve	1/4 NPT
Electrical connection	Solenoid coil type MD-... , coil can be ordered as an accessory
Nominal size	13.5 mm
Valve function	2/2-way, closed, monostable
Flow direction	Non-reversible
Medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases Water Neutral fluids
Medium pressure, valve for liquid media	0.5 bar...6 bar
Medium pressure, valve for gaseous media	0.5 bar...10 bar
Pressure difference	0.5 bar
Type of piloting	Pilot actuated
Max. viscosity	22 mm <sup>2</sup> /s
Media temperature	-10 °C...60 °C
Media temperature for fluids	5 °C...50 °C
Ambient temperature	-10 °C...60 °C
Flow rate Kv	1.6 m <sup>3</sup> /h
Standard nominal flow rate (standardised to DIN 1343)	1400 l/min
Switching time on	8 ms
Switch-on time for fluids	100 ms

Feature	Value
Switching time off	10 ms
Switch-off time for fluids	200 ms
b value	0.3
C value	6 l/sbar
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material housing	Brass
Material number housing	2.0402
Material seals	NBR
Material plunger tube	High-alloy steel
Product weight	500 g
Corrosion resistance class CRC	1 - Low corrosion stress
Max. tightening torque for cover screw	20 Nm
Max. tightening torque for connecting thread	35 Nm
Max. tightening torque for coil fastening	0.5 Nm