

Round cylinder DSNU-3/4"-12"-PPV-A

Part number: 546405

FESTO



Data sheet

Feature	Value
Stroke	12 in
Piston diameter	3/4"
Piston rod thread	5/16-24 UNF-2A
Based on standard	ISO 6432
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Piston-rod end	Male thread
Design	Piston Piston rod
Position detection	Via proximity switch
Variants	Piston rod at one end
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-4 °F...176 °F
Impact energy in end positions	0.147 ft-lbf
Cushioning length	0.67 in
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	35.6 lbf
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	42.4 lbf
Moving mass for 0 mm stroke	1.55 oz
Additional moving mass per 10 mm stroke	0.141 oz
Basic weight for 0 mm stroke	6.59 oz
Additional weight per 10 mm stroke	0.254 oz
Type of mounting	With accessories
Pneumatic connection	1/8 NPT
Material cover	Wrought aluminium alloy

Feature	Value
Material seals	NBR TPE-U(PU)
Material piston rod	High-alloy stainless steel
Material cylinder barrel	High-alloy stainless steel