


Round cylinder ESNU-1 5/8"-P-A

Part number: 548469

FESTO



Data sheet

Feature	Value
Stroke	0.4 in...2 in
Piston diameter	1 5/8"
Piston rod thread	1/2-20 UNF-2A
Based on standard	ISO 6431
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Piston-rod end	Male thread
Design	Piston Piston rod
Position detection	Via proximity switch
Variants	Piston rod at one end
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Single-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-4 °F...176 °F
Impact energy in end positions	0.516 ft-lbf
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	155 lbf
Moving mass for 0 mm stroke	8.11 oz
Additional weight per 10 mm stroke	0.564 oz
Type of mounting	With accessories
Pneumatic connection	1/4 NPT
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR TPE-U(PU)
Material piston rod	High-alloy stainless steel
Material cylinder barrel	High-alloy stainless steel