

Round cylinder DSNU-2"- -PPV-A

Part number: 548540

FESTO



Data sheet

Feature	Value
Stroke	0.4 in...20 in
Piston diameter	2"
Piston rod thread	5/8-18 UNF-2A
Based on standard	ISO 6431
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Piston-rod end	Male thread
Design	Piston Piston rod
Position detection	Via proximity switch
Variants	Piston rod at one end
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-4 °F...176 °F
Impact energy in end positions	0.738 ft-lbf
Cushioning length	0.79 in
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	198 lbf
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	236 lbf
Moving mass for 0 mm stroke	14.6 oz
Additional weight per 10 mm stroke	0.882 oz
Type of mounting	With accessories
Pneumatic connection	1/4 NPT
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR TPE-U(PU)

Feature	Value
Material piston rod	High-alloy stainless steel
Material cylinder barrel	High-alloy stainless steel