


# Rotary indexing table DHTG-65-3-A

Part number: 555448

**FESTO**



## Data sheet

Feature	Value
Size	65
Parallelity poppet valve	0.04 mm
Axial eccentricity poppet valve	0.02 mm
Concentricity poppet valve	0.02 mm
Repetition accuracy of swivel angle	0.03 deg
Cushioning	Shock absorber, hard characteristic curve, adjustable
Mounting position	optional
Mode of operation	Double-acting
Design	Gear coupling Rack and pinion Force pilot operated motion sequence
Position detection	Via inductive sensors
Pitch	3
Operating pressure	0.3 MPa...0.8 MPa 3 bar...8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C...80 °C
Sound pressure level	70 dB(A)
Degree of protection	IP54
Ambient temperature	5 °C...60 °C
Mass moment of inertia	160 kgcm <sup>2</sup>
Max. axial force static	1000 N
Max. pull-out torque static	100 Nm
Max. radial force static	2000 N

Feature	Value
Max. tangential torque static	100 Nm
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	2.1 Nm
Product weight	1900 g
Type of mounting	Via through-hole and centring sleeve
Pneumatic connection	Female thread M5
Material poppet valve	Galvanised steel
Note on materials	RoHS-compliant
Material stops	Galvanised steel
Material cover	Wrought aluminium alloy
Material seals	NBR TPE-U(PU)
Material housing	Wrought aluminium alloy