


Swivel/linear unit DSL-16- -270-CC-A-S20-KF-B

Part number: 556616

FESTO



Data sheet

| Feature | Value |
|--|--|
| Cushioning angle | 15 deg |
| Rotation angle adjustment range | 0 deg...246 deg |
| Stroke | 10 mm...100 mm |
| Piston diameter | 16 mm |
| Swivel angle | 0 deg...246 deg |
| Cushioning | Shock absorber at both ends Elastic cushioning rings/plates at both ends |
| Mounting position | optional |
| Fine adjustment | -3 deg |
| Mode of operation | Double-acting |
| Design | Vane |
| Position detection | Via proximity switch |
| Variants | Through, hollow piston rod |
| Protection against torque/guide | Via ball bearings |
| Operating pressure | 2.5 bar...8 bar |
| Max. impact speed | 500 mm/s |
| Max. swivel frequency at 0.6 MPa (6 bar, 87 psi) | 1.5 Hz |
| Rotary angle backlash | 0.05 deg |
| Repetition accuracy | 0.1 deg |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C...60 °C |
| Dynamic load torque | 0.17 Nm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 73.5 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 103.5 N |
| Theoretical torque at 0.6 MPa (6 bar, 87 psi) | 1.25 Nm |
| Permissible mass moment of inertia | 0.0007 kgm ² |
| Product weight | 750 g |
| Basic weight for 0 mm stroke | 750 g |

| Feature | Value |
|------------------------------------|---|
| Additional weight per 10 mm stroke | 33 g |
| Type of mounting | Clamped in T-slot Via male thread Either: |
| Pneumatic connection | M5 |
| Material cover | Wrought aluminium alloy Anodised |
| Material seals | TPE-U(PU) |
| Material housing | Wrought aluminium alloy Smooth anodised |
| Material piston rod | Tempered steel |