

# Compact cylinder ADN-4"-1/2"-I-P-A

Part number: 557180

FESTO



## Data sheet

Feature	Value
Stroke	0.5 in
Piston diameter	4"
Piston rod thread	1/2-20 UNF-2B
Based on standard	ISO 21287
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Double-acting
Piston-rod end	Female thread
Design	Piston Piston rod Profile barrel
Position detection	Via proximity switch
Variants	Piston rod at one end
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar 14.5 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-4 °F...176 °F
Impact energy in end positions	1.84 ft-lbf
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	1017 lbf
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	1059 lbf
Moving mass for 0 mm stroke	20.2 oz
Additional moving mass per 10 mm stroke	3.47 oz
Basic weight for 0 mm stroke	76.3 oz
Additional weight per 10 mm stroke	0.885 oz
Type of mounting	Either: With through-hole Via female thread With accessories
Pneumatic connection	1/8 NPT

Feature	Value
Material collar screws	Steel
Material cover	Die-cast aluminium, coated
Material dynamic seals	TPE-U(PU)
Material piston rod	High-alloy steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy